



1

2

d ₁	l ₁ Nominal length						l ₂		d ₂		d ₃	d ₄	d ₅	h	k
	MS pivot	KU pivot	MS pivot	KU pivot	MS pivot	KU pivot									
M 5	10	15	20	25	-	0,5	1	3	3	19	9	12	14	8	
M 6	10	16	20	25	30	1	1,3	4	3,5	24	12	14	16,5	9,5	
M 8	20	25	30	40	-	1,5	1,6	6	5	30	14	16	19,5	11	
M 10	20	25	30	45	55	2	1,9	8	6,5	36	16	18	22,5	12,5	

Specification

- Plastic Technopolymer (Polyamide PA)
Black, shiny finish
- Threaded stud
Stainless steel AISI 304 Cu
- Pivot
 - Brass **MS**
 - Plastic (Polyacetal POM) **KU**
- *Plastic Characteristics* → Page 2158
- *Stainless Steel Characteristics* → Page 2166
- RoHS

3

Information

Knurled screws GN 421.10 with pads in brass or plastic are used in applications, where marks and damage on the workpiece are unacceptable.

see also...

- *Star Knobs GN 6336.10 (with Pivot)* → Page 548
- *Knurled Screws GN 7336.5 (with Pivot)* → Page 627
- *Flat Knurled Screws GN 653.10 (with Pivot)* → Page 650
- *Knurled Screws GN 421.10 with Loss Protection GN 111.7* → Page 2084

How to order

GN 421.10-M8-25-MS

1	d ₁
2	l ₁
3	Material (Pivot)