



3 Type

- E** with threaded blind bore
- C** with blind bore H7

1 d_1	2 d_2 Thread	2 d_3 H7 Bore	d_4	$h_1 \approx$	$h_2 \approx$	t min.
40	M 8	B 8	14	24	12	15
50	M 10	B 10	18	30	16,5	18
60	M 12	B 12	20	37,5	20	22

Specification

- **GN 5334**
AISI 304 (A2)
 - **GN 5334.4**
Stainless Steel AISI 316L (A4)
- This information applies to both standards:
- Knob drawn from Stainless Steel-Sheet
 - Hub welded
 - matte shot-blasted
- *Cross holes GN 110 → Page 1422*
 - *ISO-Fundamental tolerances → Page 1479*
 - *Stainless Steel characteristics → Page 1489*
- RoHS

Information

The original ELESA design with 5 recess grips is typical for GN 5334 / GN 5334.4 Stainless Steel-Star knobs.

This form gives these grips an appealing look and additionally allows a high torque to be achieved.

see also...

- *Stainless Steel-Triangular knobs GN 5339.5 → Page 427*
- *Stainless Steel-Star knobs GN 5335 → Page 416*
- *Stainless Steel-Wing nuts GN 834 → Page 436*
- *Stainless Steel-Star knobs DIN 6336 → Page 396*
- *Stainless Steel-Hand knobs DIN 6335 → Page 420*
- *Stainless Steel-Three-lobe knobs GN 5345 → Page 428*

How to order (Stainless Steel AISI 304, A2)

GN 5334-50-M10-E

1	d_1
2	d_2 (d_3)
3	Type

How to order (Stainless Steel AISI 316L, A4)

GN 5334.4-40-B8-C

1	d_1
2	d_3 (d_2)
3	Type