



3 Type

- E** With threaded blind bore
- D** With threaded through bore

1

2

d ₁	d ₂			GN 5337.5 Type E	d ₃	d ₄	h ₁ +1	h ₂ +1	h ₃	t ₁ min.	t ₂
	GN 5337 Type E		Type D								
32	M 6	-	-	M 6	-	19	23	11	-	12	-
40	M 6	M 8	M 8	M 8	14	21	27	12	1,5	13	18
50	M 8	M 10	M 10	M 10	16	25	33	14	1,5	17	22
60	M 10	M 12	M 12	M 12	17	27	37	17	1,5	20	26
70	M 12	-	M 12	-	17	30	44	20	1,5	20	26
85	M 16	-	M 16	-	24	35	54	30	2	22	35

Specification

- Plastic
Duroplast (PF)
- Temperature resistant up to 110 °C
- Black, shiny finish
- **GN 5337**
Bushing
Brass
- **GN 5337.5**
Bushing
Stainless steel AISI 303
- *Plastic Characteristics* → Page 2158
- *Stainless Steel Characteristics* → Page 2166
- RoHS

Information

Star knobs GN 5337 / GN 5337.5 meet highest quality requirements. Due to a special manufacturing process the mould parting line can be avoided.

see also...

- *Star Knobs GN 5337.2 (Technopolymer)* → Page 560
- *Star Knobs GN 5337.4 (Technopolymer)* → Page 564

How to order (Bushing, brass)

GN 5337-40-M8-D

- 1** d₁
- 2** d₂
- 3** Type

How to order (Bushing, stainless steel)

GN 5337.5-50-M10-E

- 1** d₁
- 2** d₂
- 3** Type