



ROSTFREI
Inox
Stainless
Steel

1 d_1	2 d_2	3 Length I		h	s	A/F	Static load in N
19	M 6	30	45	14	1,5	3	240
25	M 6	30	45	16	1,5	3	540
32	M 8	40	65	18	2	4	840
38	M 8	40	65	20	2	4	920
50	M 10	45	70	22	2,5	5	2500
64	M 10	45	70	26	2,5	5	3700

Specification

- **GN 439**
Steel
 - Tensile strength class 5
 - zinc plated, blue passivated
- **GN 439.5**
Stainless Steel AISI 304
- Rubber underlay
Acrylonitrile butadiene rubber (NBR)
 - vulcanized
 - black
 - temperature resistant up to 120 °C
 - Hardness Shore A **70**
- *Strength values of screws* → Page 1481
- *Elastomer characteristics* → Page 1483
- *Stainless Steel characteristics* → Page 1489
- RoHS

On request

- other spindle diameters and lengths

Information

GN 439 / GN 439.5 levelling feet are used for installing smaller machines, systems or devices.

Thanks to the rubber underlay, they have a damping, noise-reducing effect and prevent surface damage. They are also designed such that the threaded spindle can absorb compressive forces. This is necessary because the retaining washer is not evenly supported during leveling.

Thanks to the stable rivet connection between the threaded spindle and the retaining washer, the introduced forces can be reliably transmitted to the rubber underlay.

How to order (Steel)

GN 439-38-M8-65-70

- | | |
|----------|----------|
| 1 | d_1 |
| 2 | d_2 |
| 3 | Length I |
| 4 | Hardness |

How to order (Stainless Steel)

GN 439.5-64-M10-45-70

- | | |
|----------|----------|
| 1 | d_1 |
| 2 | d_2 |
| 3 | Length I |
| 4 | Hardness |