



ELESA Original design VC.692



d ₁	d ₂		CL		d ₃	h ₁	h ₂	t min.
	black			CR				
25	M 5	M 6	-	-	12	20	10	10
32	M 5	M 6	M 6	M 6	14	22,5	12,5	10
40	M 6	M 8	M 8	M 8	15	26	14	13
50	M 8	M 10	M 10	M 10	18	31	17	17
60	M 10	M 12	M 12	M 10	21	37	21	20

Specification

- Standard version
 - Plastic
 - Technopolymer (Polyamide PA)
 - glass fiber reinforced
 - temperature resistant up to 130 °C
 - black, matte
 - Bushing Stainless Steel AISI 303
 - Cleanline version CL
 - Plastic
 - Technopolymer (Polyamide PA)
 - glass fiber reinforced
 - temperature resistant up to 130 °C
 - white, RAL 9002
 - Bushing Stainless Steel AISI 303
 - Chrome-plated version CR
 - Plastic
 - Technopolymer (Polyamide PA)
 - glass fiber reinforced
 - temperature resistant up to 80 °C
 - chrome-plated
 - Bushing brass
- *Plastic characteristics* → Page 1483
 • *Stainless Steel characteristics* → Page 1489
 • RoHS

On request

- Bushing steel zinc plated, blue passivated

Information

The underside of the knob GN 5337.4 is not recessed or hollowed. This means that if they are fitted with a Stainless Steel bush they will meet the standards and requirements for hygiene applications.

The chrome plating lends the star knobs a metallic appearance. The surface is hard and smooth. Features making these star knobs particularly suitable for applications where high hygiene standards are required.

If exposed to aggressive media, the chrome layer of the star knobs has an advantageous effect. Test series reports on the chemical resistance are available.

How to order	1	d ₁
	2	d ₂
GN 5337.4-40-M8		

How to order (Cleanline)	1	d ₁
	2	d ₂
	3	Finish
GN 5337.4-40-M8-CL		