



<sup>1</sup> d <sub>1</sub>	<sup>2</sup> d <sub>2</sub> H7	d <sub>3</sub> -0,3	d <sub>4</sub>	Length l	s -0,15	t min.
M 6	8	18	8,5	19	9	9
M 8	10	20	11	24	12	11
M 10	12	25	13,5	28	14	14
M 12	16	32	16	34	17	16

### Specification

- Steel
  - Property class 5
  - Blackened
- *ISO Fundamental Tolerances* → Page 2151
- *Strength Values of Nuts* → Page 2152
- RoHS

### Information

In combination with grub screws (i.e. DIN 913 or DIN 6379) swing nuts GN 444.2 can be used together as swing bolts in varying lengths.

In addition, used with a cap screw DIN 912, a swiveling clamping screw can be produced.

Dimensions d<sub>2</sub>, d<sub>3</sub> and s are identical to DIN 444.

For swing nut thread sizes M6, M8 M10 and M12, cylinder head shoulder bolts GN 732.1 can be used as bearing pins.

see also...

- *Cylinder Head Shoulder Bolts GN 732.1* → Page 1057
- *Joint Pieces GN 752 (for Fork Joints)* → Page 1667
- *Studs DIN 6379* → Page 1166

How to order	<sup>1</sup> d <sub>1</sub>
	<sup>2</sup> d <sub>2</sub>

**GN 444.2-M10-12**

3.1  
3.2  
3.3  
3.4  
3.5  
3.6  
3.7  
3.8  
3.9

