



1 2

d ₁	Length l								d ₂	d ₃	h	k
	4	6	8	10	-	-	-	-				
M 2	4	6	8	10	-	-	-	-	9	4,5	5,3	2
M 2,5	4	6	8	10	12	-	-	-	11	5	6,5	2,5
M 3	6	8	10	12	16	20	-	-	12	6	7,5	2,5
M 4	5	8	10	12	16	20	25	-	16	8	9,5	3,5
M 5	6	8	10	12	16	20	25	30	20	10	11,5	4
M 6	8	10	12	16	20	25	30	35	24	12	15	5
M 8	12	16	20	25	30	35	40	-	30	16	18	6
M 10	12	15	20	25	30	35	40	-	36	20	23	8

Specification

- Steel
 - Tensile strength class 5
 - visible face fine turned
 - blackened
 - zinc plated, blue passivated
- Stainless Steel
 - AISI 303
 - matte shot-blasted
- Stainless Steel characteristics → Page 1489
- Strength values of screws → Page 1481
- RoHS

3

Information

Knurled screws DIN 464 are turned entirely from a single piece. The thread of the screw generally extends up to the shoulder and ends in a runout without recess.

They are suitable for universal use and can be quickly tightened and loosened without tools.

see also...

- Flat knurled screws DIN 653 → Page 459
- Knurled screws GN 653.2 (with recessed stud for loss protection) → Page 461
- Stainless Steel-Knurled screws GN 535 → Page 452
- Knurled screws DIN 464 with loss protection GN 111.7 → Page 1426

How to order (Steel, blackened)	1	d ₁
DIN 464-M6-20	2	Length l

How to order (Steel, zinc plated)	1	d ₁
DIN 464-M2,5-6-ZB	2	Length l
	3	Finish

How to order (Stainless Steel)	1	d ₁
DIN 464-M10-35-NI	2	Length l
	3	Material

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

