


elesa

Original design VTT-SST-SAN



Inox
Stainless
Steel



¹ d ₁	² d ₂	d ₃	h ₁	h ₂	t min.
40	M 8	16	27	13,5	13
50	M 10	19	30	15	17

Specification

Knob

- Plastic, Polyamide (PA)
- Glass fiber reinforced
- Operating temperature -30 °C to +130 °C
- Black-gray, RAL 7021, matte finish
- White, RAL 9016, matte finish

- SGA
- WSA

Threaded bushing

Stainless steel AISI 304

RoHS

Three-lobed knobs GN 5342 are manufactured from an antimicrobial plastic. Adding a silver-based substance has created a natural active agent that helps to prevent the growth of bacteria. Even after repeated cleaning with soap or solvent, the antimicrobial effect of this additive will not diminish. Sterilising at temperatures below 130 °C will also have no effect on the antimicrobial property.

With these properties, the handles are the perfect choice for use in medical engineering, in the food and the pharmaceutical industry, and in general wherever hygiene is of great importance.

see also...	Page
GN 5337.4 Star Knobs (Plastic, Threaded Bushing Stainless Steel)	QVX

Technical Information

Product family Sanline	QVX
Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX

How to order

GN 5342-40-M8-WSA

¹ d ₁	
² d ₂	
³ Oberflächen	

