



3 Type

- F With fixed handle
- D With revolving handle

Length l	1 s H11		2 e min.		2 d ₁ H7 Bore	d ₂	h ₁	h ₂	h ₃ ≈	h ₄ ≈		Ø Handle
	Square	-	(Column 1)	(Column 2)						Type D	Type F	
63	V 10	-	13,1	-	-	20	20	11	32	54,5	50	16
80	V 10	V 12	13,1	16,1	B 8	24	24	13	38	61	56	18
100	V 12	V 14	16,1	18,1	B 10	28	28	13	48	67	64	20
125	V 14	V 17	18,1	22,2	B 10	34	34	14	55	76	72	22
160	V 17	V 19	22,2	25,2	B 14	38	38	14	65	83	80	25
200	V 19	V 22	25,2	28,2	B 17	44	44	21	78	96,5	90	28
250	V 22	V 24	28,2	32,2	B 17	48	48	21	90	105,5	100	32
315	V 24	V 27	32,2	36,2	B 20	54	54	26	105	117	112	36

Specification

Body

Cast iron (GGG)

- Powder coated
- Black, textured finish
- Face of the hub machined

Fixed handle DIN 39 for type F

Steel

Zinc plated, blue passivated

Revolving handle DIN 98 for type D

Steel

Zinc plated, blue passivated

RoHS

The hub bores d₁ H7 are not provided for in the official standard sheet.

see also...

DIN 469 Cranked Handles (Straight) Page QVX

Technical Information

Cross holes GN 110 QVX

Squares DIN 79 QVX

ISO Fundamental Tolerances QVX

How to order

DIN 468-100-V14-F

- 1 Length l
- 2 s (d₁)
- 3 Type

