



ELESA original design IF / IFF

**4 Type**

- A** with hand guard, one side
- B** with hand guard, both sides

<b>1</b> $d_1$	<b>2</b> $d_2$	<b>3</b> $l_2$	$d_3$	$d_4$	$l_1$	$l_3$	$l_4$	$t$
30	M 8	20	64	46	112	4	4	20
30	M 10	20	64	46	112	4	4	18

**Specification**

- Plastic  
Technopolymer (Polyamide PA)  
- glass fiber reinforced  
- temperature resistant up to 130 °C  
- black, matte
- Bushing  
Brass
- Threaded stud  
Steel  
zinc plated, blue passivated
- *Plastic characteristics* → Page 1483
- RoHS

**Information**

GN 539.2 cylindrical handles are used as handles for electronic tools such as angle grinders, percussion drills etc. Their special feature is the hand guard on one or both sides.

see also...

- *Cylindrical handles GN 519* → Page 52

How to order (Bushing)

**GN 539.2-30-M8-A**

- 1**  $d_1$
- 2**  $d_2$
- 3** Type

How to order (Threaded stud)

**GN 539.2-30-M8-20-A**

- 1**  $d_1$
- 2**  $d_2$
- 3**  $l_2$
- 4** Type