



Length l	d <sub>1</sub> H7 Bore	s H11 Square	d <sub>2</sub>	d <sub>3</sub>	h <sub>1</sub>	h <sub>2</sub>	h <sub>3</sub>	h <sub>4</sub>	h <sub>5</sub> ≈	Ø Handle GN 598
100	B 12	V 12	27	30	28	17	13	19,5	67,5	23
125	B 14	V 14	32	35	34	22	14	19,5	67,5	23
160	B 17	V 17	35	39	38	26	16	19,5	82,5	26

**Specification**

**Body**

- Aluminum
- Powder coated
- Black, textured finish
- Contact face of hub machined

**Retractable Handle GN 598.3**

- Plastic, phenolic resin (PF)
- Black, shiny finish
- Retractable Mechanism
- Steel, blackened

RoHS

**On request**

- with Retractable Handle GN 598.5 (Retractable Mechanism Stainless Steel)

The handle of the cranked handles with retractable handle GN 471. 3 is locked in a tapered bore in the operating position.

For tilting, the handle must first be pulled out of the taper in axial direction. A pressure spring holds the handle in both end positions. When folded out, it automatically re-engages.

see also... **GN 570.3** Cranked Handles with Retractable Handle (Plastic, with Blind Bore) **Page QVX**

**Technical Information**

Cross holes GN 110 **QVX**  
 Squares DIN 79 **QVX**  
 ISO Fundamental Tolerances **QVX**

How to order

**GN 471.3-125-V14**

1 Length l

2 s (d.)

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4

