



View of magnetic surface



2

d ₁	d ₂	h	Nominal adhesive forces in N
10	8	9	4
18	14	8	10
25	22	8,5	14
30	28,5	8,5	27
36	32,5	7,9	35
40	36	8	35

Specification

Magnet
NdFeB **ND**
Neodymium, iron, boron
Operating temperature up to 80 °C

Housing
Plastic

- White, RAL 9003 ○ WS
- Gray, RAL 7040 ○ GR
- Black, RAL 9004 ● SW
- Red, RAL 3031 ● RT

RoHS

On request

- Other colors
- Magnet hard ferrite
- With custom imprint

Magnets GN 53.1 work in combination with the flat, disk-shaped plastic housing as a system for holding documents, templates, drawings etc. that are used in technical environments.

The neodymium magnets used are characterized by a high magnetic force.

see also...

	Page
GN 53.2 Magnets (Rectangular-Shaped)	QVX
GN 53.3 Magnets (Disk-Shaped, with Handle)	QVX
GN 53.4 Magnets (Disk-Shaped, with Handle)	QVX
GN 51.7 Magnets (With Knob / with Key Ring)	QVX

Technical Information

More Information on Retaining Magnets	QVX
---------------------------------------	-----

Accessory

GN 70 Holding Disks	QVX
GN 70.1 Adhesive Disks	QVX

How to order

GN 53.1-ND-30-RT

1	Material
2	d ₁
3	Color

