



2 Bore
B without keyway
K with keyway

Length l	d ₁ H7 Bore	d ₂	h	b P9	t
75	16	32	24	5	17,3
90	18	34	26	6	19,7
110	20	36	30	6	21,7
135	22	42	32	6	23,7
165	24	44	36	8	25,7

Specification

- Body
Cast iron (GGG)
- deburred and shot-blasted
- hub machined
- Handle
Steel, blackened
- Indexing pin
Steel, hardened
- [Keyway P9 DIN 6885 Page 2 → Page 1421](#)
- [ISO-Fundamental tolerances → Page 1479](#)
- **RoHS**

Information

Indexing cranked handles GN 558 are for positioning mechanisms. Standard machine elements for positioning of spindles:

see also...

- [Indexing mechanisms GN 200 → Page 272](#)
- [Indexing levers GN 215 → Page 278](#)
- [Adjustable knob GN 700 → Page 276](#)

How to order

GN 558-75-K16

1	Length l
2	Bore
3	d ₁

