



1

2

2

Length l	d ₁ H7 Bore	s H11 Square	d ₂	d ₃	h ₁	h ₂ ≈	h ₃	h ₄	h ₅ ≈	Ø Handle
80	B 10	V 10	23	30	19,5	4	25,5	4,3	43	16
100	B 12	V 12	26,7	35	23,5	5,5	29,5	4,2	57,5	18
125	B 14	V 14	28	37	30,5	10,5	36,5	4,2	76,5	24

Specification

3

- Body
Aluminum
 - plastic coated
black, RAL 9005, textured finish ● SW
 - silver, RAL 9006, textured finish ● SR
 - hub machined
- Hub cover
light gray
- Retractable handles GN 798.3
 - Plastic, Technopolymer
black, matt finish
 - Retractable mechanism
Steel, blackened
- Retractable handles GN 798.5
Plastic, Technopolymer
black, matt finish
Retractable mechanism
Stainless Steel
 - Axle parts AISI 303
 - Flat base
Sintered Steel AISI 316
- Square DIN 79 → Page 1242
- Cross holes GN 110 → Page 1422
- ISO-Fundamental tolerances → Page 1479
- Stainless Steel characteristics → Page 1489
- RoHS

Information

The handpiece of the cranked handle GN 472.3 / GN 472.5 is locked in a tapered bore in the operating position.

For tilting, the handle must first be pulled out of the taper in axial direction.

A compression spring holds the handle in both end positions. When folded out, it automatically re-engages.

How to order (Retractable mechanism steel)

1	Length l
2	s (d ₁)
3	Color

GN 472.3-100-V12-SR

How to order (Retractable mechanism Stainless Steel)

1	Length l
2	d ₁ (s)
3	Color

GN 472.5-125-B14-SW