



2 Type

- A** Closed type
- B** Open ended type, mounting from the back (threaded blind bore)
- C** Open ended type, mounting from the operator's side

1

l_1	a_1	a_2	a_3	b_1	b_2	d_1	d_2	h_1	h_2	h_3	h_4	h_5	l_2	$l_3 \pm 0,2$	l_4	l_5	l_6	l_7	t_1 min.	t_2 min.	t_3
162	38	19	40	25	28	M 8	8,3	55	57	36	38	28	128	140	8	22	10	20	12	16	8

Specification

Handle

- Aluminum
- Powder coated
- Black, RAL 9005, textured finish
- Silver, RAL 9006, textured finish

- SW
- SR

Cover cap for type C

- Plastic
- Black for SW
- Light gray for SR

RoHS

A special characteristic of the cabinet U-handles GN 559 is the thumb rest pad on the front of the leg. At the same time the extended leg offers an open ended version with wide access.

The fastening bores of type C are closed by a cover cap following the handle installation. The cover cap is included in the delivery contents.

Cabinet U-handles GN 559 are known for their high stability. They are fixed by two M8 screws whereby type A offers two alternative hole centers (l_2 or l_3).

Technical Information

Load Rating Information

Page

QVX

How to order

GN 559-162-B-SW

- 1** l_1
- 2** Type
- 3** Finish

1.1 1.2 1.3 1.4 2.1 2.2 2.3 2.4

