



Clamping kit GN 511




Application example



Retaining magnet GN 51.6



d ₁ Bore for shaft tol. h11	b ₁	b ₂	d ₂	d ₃ Clamping thread	d ₄ For screw	l ₁	l ₂	l ₃	l ₄	m	s Square	Clamping kits for d ₃ 
B 8	14	29	31,5	M 4	M 4	20	7	7	3	22	-	GN 511-M4-14
B 10	16	35	38	M 5	M 5	24	8	8	2,5	27	8	GN 511-M5-16
B 12	16	35	38	M 5	M 5	25	8	8	2,5	27	10	GN 511-M5-16
B 15	20	41	45	M 6	M 6	30	10	10	4	32	12	GN 511-M6-20
B 16	20	41	45	M 6	M 6	31	10	10	4	32	-	GN 511-M6-20
B 20	25	44	50	M 6	M 6	35	12,5	12,5	6,5	36	16	GN 511-M6-25

Specification

- Aluminum
- Matte finish, tumbled **MT**
- Black anodized **ELS**

- Socket cap screws DIN 912
Stainless steel AISI 304
- ISO Fundamental Tolerances → Page 2151
- Stainless Steel Characteristics → Page 2166
- RoHS

Accessory

- Clamping Kits GN 511 → Page 1804



Information

Base plate mounting clamps GN 473 have a horizontal and a vertical clamping bore. The vertical clamping bore is additionally fitted with a square.

The bore distance m corresponds to base plate mounting clamps GN 473, base plate swivel mounting clamps GN 485 and flanged mounting bolts GN 480 as well as retaining magnets GN 51.6.

In the standard version, the clamping screws are socket cap screws with hexagonal socket DIN 912. They can be replaced by clamping kits GN 511 (article code see table of dimensions).

see also...

- Product Family Standard Parts for Profile Systems → Page 18
- Retaining Rods / Retaining Tubes GN 480.1 → Page 1833
- Flanged Connector Clamps GN 145 → Page 1725
- Base Plate Mounting Clamps GN 175 (Plastic) → Page 1807
- Assembly Sets for Profile Systems 30 / 40 GN 965 → Page 2086
- Assembly Sets for Profile Systems 30 / 40 / 45 GN 968 → Page 2096

How to order

GN 473-B12-MT

1 d₁

2 Finish