



ELESA Original design MT-AT

1

2

Length l	d ₁ H9 Bore	d ₂	d ₃	d ₄	h ₁	h ₂	h ₃	h ₄ ≈	t min.	Ø Handle
50	B 6	15	18	23	30	20,5	9	35	16	14
64	B 8	15	20	27	32	18,5	13,5	45	18	16
80	B 10	18	23,5	30	36	23,5	14	60	23	18
100	B 12	18	24	34	40	24,5	14,5	65	22	22
130	B 14	26	34	40	49	34	15,5	65	28	22
160	B 16	26	34	45	55	38	17,5	80	28	24

Specification

- Body
Plastic
Technopolymer (Polyamide PA)
- glass fiber reinforced
- temperature resistant up to 90 °C
- black, matte

- Hub bushing
Steel, blackened
- Revolving handles
- Plastic, Technopolymer
black, matte
- Spindle steel
zinc plated, blue passivated

- Cross holes GN 110 → Page 1422
- ISO-Fundamental tolerances → Page 1479
- Plastic characteristics → Page 1483

- RoHS

Information

Cranked handles GN 570.2 are connected to a shaft by means of a cross pin.

Owing to the small, non-protruding steel bushing, these cranked handles are lower priced than GN 570.

How to order

GN 570.2-80-B10

1 Length l

2 d₁