





Countersunk for socket cap screw DIN 912



Clamping kit GN 511



Application example



Retaining magnet GN 51.6

1

d <sub>1</sub> Bore for shaft tol. h11	d <sub>2</sub> For screw	k	l <sub>1</sub>	l <sub>2</sub>	m	s Square	Clamping kits for d <sub>2</sub>
B 8	M 4	14	31,5	10	22	-	GN 511-M4-20
B 10	M 5	16	38	10,5	27	8	GN 511-M5-25
B 12	M 5	16	38	10,5	27	10	GN 511-M5-25
B 15	M 6	20	45	14	32	12	GN 511-M6-25
B 16	M 6	20	45	14	32	-	GN 511-M6-25
B 20	M 6	25	50	19	36	16	GN 511-M6-32

**Specification**

- Aluminum
  - Matte finish, tumbled **MT**
  - Black anodized **ELS**
- ISO Fundamental Tolerances → Page 2151
- Stainless Steel Characteristics → Page 2166
- RoHS

**Accessory**

- Clamping Kits GN 511 → Page 1804

2

**Information**

Mounting clamps GN 477 have no thread. Mounting or clamping is made via two threads on the attachment side.

The bore distance m corresponds to base plate mounting clamps GN 473, base plate swivel mounting clamps GN 485 and flanged mounting bolts GN 480 as well as retaining magnets GN 51.6.

see also...

- Product Family Standard Parts for Profile Systems → Page 18
- Retaining Rods / Retaining Tubes GN 480.1 → Page 1833
- Flanged Connector Clamps GN 145 → Page 1725
- Assembly Sets for Profile Systems 30 / 40 GN 965 → Page 2086
- Assembly Sets for Profile Systems 30 / 40 / 45 GN 968 → Page 2096

How to order

**GN 477-B12-MT**

1 d<sub>1</sub>

2 Finish