



ELESA Original design MR.

1 2

l_1	d_1			d_2	d_3	d_4	h_1	h_2	h_3	h_4 Stroke	t min.
42	M 4	M 5	M 6	12	18	16	27	6	32	3,5	10
63	M 6	M 8	-	15	23	20	34	8	43	4	12
80	M 8	M 10	M 12	19	28	24	42	10	54	4	15
100	M 12	M 14	M 16	25	33	31	48	12	65	5	20

Specification

- Handle
Plastic
Technopolymer (Polyamide PA)
- glass fiber reinforced
- temperature resistant up to 130 °C
- black, RAL 9005, matte ● **SW**
- Threaded bushing and retaining screw
Steel, blackened
- *Plastic characteristics* → Page 1483
- **RoHS**

On request

- different colors

3

Information

Adjustable hand levers GN 500 besides their good design, offer the advantage that the plastic material used is fully penetrated by the colour and will not show any discolouring through abrasion or use.

When pulling the handle, the serration frees itself and can be re-located into any required position. When „releasing“ the lever the serration re-engages automatically.

How to order

GN 500-63-M8-SW

1	l_1
2	d_1
3	Color

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

