



ELESA Original design BT.p



1 d_1	2 d_2	3 Length I		3 Length I Plastic ESD						d_3	h	k
12	M 4	10	16	-	-	-	-	-	-	9,5	11,5	7,5
12	M 5	10	16	-	-	-	-	-	-	9,5	11,5	7,5
16	M 4	10	16	20	30	-	-	-	-	11	13	8
16	M 5	10	16	-	-	-	10	16	-	11	13	8
20	M 5	10	16	20	25	-	-	-	-	12	16	10
20	M 6	10	16	25	40	-	10	16	25	12	16	10
25	M 6	10	-	-	-	-	-	-	-	11,5	16	8
25	M 6	16	20	25	30	50	-	-	-	16	19	11
25	M 8	16	25	-	-	-	16	25	-	16	19	11
32	M 8	16	20	25	30	40	-	-	-	17	22	13
32	M 10	20	25	30	40	-	20	30	-	17	22	13
40	M 10	30	-	-	-	-	-	-	-	19	27	14
50	M 10	30	-	-	-	-	-	-	-	22	28,5	15

Specification

- Plastic Technopolymer (Polyamide PA) - reinforced - temperature resistant up to 130 °C - black, matte finish

- Threaded stud Steel zinc plated, blue passivated

- Plastic Technopolymer (Polyamide PA) electrically conductive (antistatic) **ESD**

• *Plastic characteristics* → Page 1483

- RoHS



Information

Knurled screws GN 591 type ESD are made of a conductive plastic which prevents an electrostatic loading. The imprint ESD defines the special antistatic properties according IEC 61340-5-1.

see also...

- *Product family ESD* → Page 17
- *Knurled nuts GN 421* → Page 449

How to order

GN 591-25-M8-25

1	d_1
2	d_2
3	Length I

How to order (Plastic ESD)

GN 591-25-M8-16-ESD

1	d_1
2	d_2
3	Length I
4	antistatic Plastic