



ELESA Original design MR-p

1 2 3

$l_1$	$d_1$	$l_2$		$d_2$	$d_3$	$d_4$	$h_1$	$h_2$	$h_4$	Stroke						
42	M 5	10	16	20	-	-	-	-	-	-	12	18	16	27	6	3,5
42	M 6	10	16	20	25	30	40	-	-	-	12	18	16	27	6	3,5
63	M 6	10	16	20	25	30	40	-	-	-	15	23	20	34	8	4
63	M 8	16	20	25	30	35	40	45	50	60	15	23	20	34	8	4
80	M 10	20	25	30	35	40	50	60	70	-	19	28	24	42	10	4
80	M 12	20	25	30	35	40	50	60	70	80	19	28	24	42	10	4
100	M 12	30	50	70	-	-	-	-	-	-	25	33	31	48	12	5
100	M 16	30	50	70	-	-	-	-	-	-	25	33	31	48	12	5

Specification

- Handle  
Plastic  
Technopolymer (Polyamide PA)  
- glass fiber reinforced  
- temperature resistant up to 130 °C  
- black, RAL 9005, matte ● SW
- Threaded stud and retaining screw  
Steel, blackened
- Plastic characteristics → Page 1483
- RoHS

On request

- different colors

4

Information

Adjustable hand levers GN 500 besides their good design, offer the advantage that the plastic material used is fully penetrated by the colour and will not show any discolouring through abrasion or use.

When pulling the handle, the serration frees itself and can be re-located into any required position. When „releasing“ the lever the serration re-engages automatically.

How to order

1	$l_1$
2	$d_1$
3	$l_2$
4	Color

GN 500-80-M10-40-SW

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4

