



elesa
Original design ERM.SST



| ¹ l ₁ | ² d ₁ Thread | | | ² d ₂ H7 Bore | | d ₃ | d ₄ | h ₁ | h ₂ | h ₃ | h ₄ Stroke | t min. |
|-----------------------------|------------------------------------|------|------|-------------------------------------|------|----------------|----------------|----------------|----------------|----------------|-----------------------|--------|
| 44 | M 4 | M 5 | M 6 | B 5 | B 6 | 10 | 14,5 | 24,5 | 3,5 | 30 | 3,5 | 8 |
| 63 | M 6 | M 8 | - | B 8 | - | 13,5 | 18 | 31 | 3,5 | 38 | 4 | 10 |
| 78 | M 8 | M 10 | M 12 | B 8 | B 10 | 16 | 21,5 | 36 | 3,5 | 46 | 4 | 14 |
| 95 | M 10 | M 12 | - | B 12 | - | 19 | 25 | 43 | 5 | 56 | 4 | 17 |

Specification

- Handle
Zinc die casting
- Powder coated
Black, RAL 9005, textured finish ● **SW**
Orange, RAL 2004, textured finish ● **OS**
Red, RAL 3000, textured finish ● **RS**
Silver, RAL 9006, textured finish ● **SR**
- Bushing and retaining screw
Stainless steel AISI 303
- ISO Fundamental Tolerances → Page 2151
- Stainless Steel Characteristics → Page 2166
- RoHS



Information

Adjustable hand levers GN 602.1 like all the products of the Ergostyle® family are renowned for their good style but also their ergonomical shape. The gently arched handle with a reinforced end of the lever gives the operator a good grip. Pulling the lever disengages the serration and allows it to be turned in either direction to reach the ideal new location. On releasing the handle the serrations re-engage automatically.

see also...

- Product Family Ergostyle® → Page 18
- Adjustable Hand Levers GN 602 (Zinc Die Casting, Bushing Steel) → Page 456
- Adjustable Hand Levers GN 604.1 (Handle Plastic, Bushing Stainless Steel) → Page 462

How to order

GN 602.1-78-M8-SW

- ¹ l₁
- ² d₁ (d₂)
- ³ Color