



¹ l ₁	² d ₁ Thread			² d ₂ H7 Bore		d ₃	d ₄	h ₁	h ₂	h ₃	h ₄ Stroke	t min.
44	M 4	M 5	M 6	B 5	B 6	10	14,5	24,5	3,5	30	3,5	8
63	M 6	M 8	-	B 8	-	13,5	18	31	3,5	38	4	10
78	M 8	M 10	M 12	B 8	B 10	16	21,5	36	3,5	46	4	14
95	M 10	M 12	-	B 12	-	19	25	43	5	56	4	17

Specification

- Handle
Zinc die casting
- Powder coated
Black, RAL 9005, textured finish ● **SW**
Orange, RAL 2004, textured finish ● **OS**
Red, RAL 3000, textured finish ● **RS**
Silver, RAL 9006, textured finish ● **SR**
- Bushing and retaining screw
Steel, blackened
- ISO Fundamental Tolerances → Page 2151
- RoHS



Information

Adjustable hand levers GN 602 like all the products of the Ergostyle® family are renowned for their good style but also their ergonomical shape.

The gently arched handle with a reinforced end of the lever gives the operator a good grip.

Pulling the lever disengages the serration and allows it to be turned in either direction to reach the ideal new location. On releasing the handle the serrations re-engage automatically.

see also...

- Product Family Ergostyle® → Page 18
- Adjustable Hand Levers GN 602.1
(Zinc Die Casting, Bushing Stainless Steel) → Page 458
- Adjustable Hand Levers GN 604 (Plastic, Bushing Steel) → Page 460

How to order

GN 602-63-M6- RS

- ¹ l₁
- ² d₁ (d₂)
- ³ Color