



<b>1</b> $l_1$	<b>2</b> $d_1$	<b>3</b> $l_2$											$d_2$	$d_3$	$h_1$	$h_2$	$h_3$	$h_4$ Stroke
30	M 5	10	16	-	-	-	-	-	-	-	-	-	12	15,5	29,5	6	30	3,5
30	M 6	10	16	20	25	30	-	-	-	-	-	12	15,5	29,5	6	30	3,5	
44	M 5	10	16	-	-	-	-	-	-	-	-	12	15,5	29,5	6	32,5	3,5	
44	M 6	10	16	20	25	30	-	-	-	-	-	12	15,5	29,5	6	32,5	3,5	
63	M 6	10	20	30	40	-	-	-	-	-	-	15	19	37,5	8	43	4	
63	M 8	16	20	25	30	35	40	45	50	60	70	15	19	37,5	8	43	4	
78	M 10	20	30	35	40	50	60	-	-	-	-	19	23	47	12	54	4	
78	M 12	30	35	40	50	70	-	-	-	-	-	19	23	47	12	54	4	
95	M 12	30	40	50	70	-	-	-	-	-	-	21,5	26,5	54,5	13	64,5	4,5	
108	M 12	30	40	50	70	-	-	-	-	-	-	25	30	54,5	11	65,5	4,5	

**Specification**

- Handle  
Plastic  
Technopolymer (Polyamide PA)  
- Glass fiber reinforced  
- Temperature resistant up to 130 °C  
- Black-gray, matte, similar RAL 7021
- Color of the releasing button (shiny finish):  
Black-gray, RAL 7021 ● **DSG**  
Orange, RAL 2004 ○ **DOR**  
Gray, RAL 7035 ○ **DGR**  
Yellow, RAL 1021 ● **DGB**  
Blue, RAL 5024 ● **DBL**  
Red, RAL 3000 ● **DRT**  
Green, RAL 6017 ● **DGN**
- Threaded stud  
Stainless steel AISI 303
- *Plastic Characteristics* → Page 2158
- *Stainless Steel Characteristics* → Page 2166
- RoHS

**Information**

Adjustable hand levers GN 603.1, like all the products of the Ergostyle® range, are renowned for their good style but also their ergonomic shape.

They are like all adjustable hand levers ideal whenever parts have to be clamped in a confined space or in a particular lever position. The centre insert is connected to the lever via serrations which can easily be disengaged.

The releasing button offers an easy disengagement. Its use is limited to applications where dismantling of the lever for installation is not required.

**see also...**

- *Product Family Ergostyle®* → Page 18
- *Adjustable Hand Levers GN 603 (with Releasing Button, Threaded Stud Steel)* → Page 469

**How to order**

<b>1</b>	$l_1$
<b>2</b>	$d_1$
<b>3</b>	$l_2$
<b>4</b>	Color (Releasing button)

**GN 603.1-63-M8-20-DOR**