



1

2

d <sub>1</sub>	l <sub>2</sub>	d <sub>2</sub>	l <sub>1</sub>	l <sub>3</sub>	l <sub>4</sub>	h <sub>1</sub>	h <sub>2</sub>
M 4	14	7,5	22	9,5	4,5	18,5	23
M 4	16	7,5	22	11,5	4,5	18,5	23
M 4	20	7,5	22	15,5	4,5	18,5	23
M 5	16	9	30	10	6	24,5	30,5
M 5	20	9	30	14	6	24,5	30,5
M 5	25	9	30	19	6	24,5	30,5
M 6	20	10,5	45	13,5	6,5	24,5	35
M 6	25	10,5	45	18,5	6,5	24,5	35
M 6	30	10,5	45	25,5	6,5	24,5	35
M 6	32	10,5	45	25,5	6,5	24,5	35

## Specification

- Handle  
Zinc die casting  
plastic coated  
silver, RAL 9006, textured finish
- Insert / Distance sleeve  
Stainless Steel AISI 303
- *Stainless Steel characteristics* → Page 1489
- RoHS

## Information

For clamp mountings, the clamping kits GN 511 replace the hexagon socket screw DIN 912. It is used on all clamping points where repeated clamping actions are required, e.g. for adjusting a stop mechanism.

The matching clamping kits for each clamping thread are listed in the dimensional tables of the clamp mountings.

How to order

GN 511-M5-25

1 d<sub>1</sub>2 l<sub>2</sub>