



ELESA Original design ERX-CR



1

2

l_1	d_1	d_2	d_3	h_1	h_2	h_3	h_4 Stroke	t min.
44	M 6	12	15,5	29,5	6	32,5	3,5	10
63	M 8	15	19	37,5	8	43	4	13
78	M 10	19	23	47	12	54	4	17
95	M 12	21,5	26,5	54,5	13	64,5	4,5	20

Specification

- Handle
Plastic
Technopolymer (Polyamide PA)
- glass fiber reinforced
- temperature resistant up to 80 °C
- chrome-plated, shiny
- Color of the releasing button
black, shiny finish
- Threaded bushing
Brass
- *Plastic characteristics* → Page 1483
- RoHS

On request

- with threaded stud

Information

Adjustable hand levers GN 603.4, like all the products of the Ergostyle® range, are renowned for their good style but also their ergonomic shape.

The gently arched handle with a reinforced end of the lever gives the operator a good grip when resting the thumb on the press button to disengage the serration for re-adjusting the lever position in either direction.

With the lever disengaged the thread insert can also be screwed in with the help of the serration.

Its use is, however, limited to applications where dismantling of the lever for installation is not required.

see also...

- *Product family Ergostyle®* → Page 17

How to order

GN 603.4-95-M12

- 1 l_1
- 2 d_1

