


View of magnetic surface



2

d <sub>1</sub>	d <sub>2</sub>	h	t <sub>1</sub>	t <sub>2</sub>	Nominal magnetic forces in N
18	M 4	6	3,5	0,8	25
22	M 4	6	4,5	0,8	38
31	M 5	6	4,5	0,8	89
43	M 4	6	4	0,8	100
57	M 5	7,5	4,5	1,2	200
66	M 6	8,5	6	1,8	250
88	M 6	8,5	6	1,8	550

**Specification**

1

3

- Steel part  
Zinc plated
- Material of the magnet  
NdFeB **ND**  
Neodymium, iron, boron  
Temperature resistant up to 80 °C
- Rubber jacket  
Elastomer (TPE)  
≈ 80 Shore A  
- Black **● SW**  
- White **○ WS**
- *Elastomer Characteristics* → Page 2158
- **RoHS**

**Information**

The retaining magnets GN 51.5 with rubber jacket form a system together with the steel part that shields and strengthens the magnet, optimally concentrating the magnetic flux on the rubberized magnetic surface.

The rubber protects sensitive surfaces from being damaged by the magnet and also delivers a high friction coefficient, resulting in high lateral displacement forces.

see also...

- *More Information to Retaining Magnets* → Page 2028
- *Retaining Magnets GN 51.3 (with Threaded Stud)* → Page 2046
- *Retaining Magnets GN 50.4 (with Internal Thread)* → Page 2037
- *Stainless Steel Retaining Magnets GN 52.5 (with Threaded Stud)* → Page 2061

**Accessory**

- Holding Disks GN 70 → Page 2072
- Adhesive Disks GN 70.1 → Page 2073

**On request**

- Other colors
- Other shore hardnesses

How to order

**GN 51.5-ND-88-SW**

1	Material
2	d <sub>1</sub>
3	Color

