



ELESA Original design



1				2				3								
l ₁		d ₁		l ₂				d ₂	d ₃	h ₁	h ₂	h ₃	h ₄ Stroke			
63	M 6	M 8	-	16	20	25	32	40	50	63	13,5	19	31	3,5	38,5	4
78	M 8	M 10	M 12	20	25	32	40	50	63	80	16	23	36	3,5	46,5	4

Specification

- Handle
Plastic
Technopolymer (Polyamide PA)
- glass fiber reinforced
- temperature resistant up to 130 °C
- black-gray, RAL 7021, matte ● **SGA**
- white, RAL 9016, matte ○ **WSA**
- Annular gear ring
Zinc die casting
- Threaded stud and retaining screw
Stainless Steel AISI 303
- Plastic characteristics
→ Main Catalogue Page 1483
- Stainless Steel characteristics
→ Main Catalogue Page 1489
- RoHS



Information

Adjustable hand levers GN 604.1 are manufactured from an antibacterial plastic.

Adding a silver-based substance has created a natural active agent that helps to prevent the growth of bacteria. Even after repeated cleaning with soap or solvent, the antibacterial effect of this additive will not diminish. Sterilising at temperatures below 130 °C will also have no effect on the antibacterial property.

With these properties, the handles are the perfect choice for use in medical engineering, in the food and the pharmaceutical industry, and in general wherever hygiene is of great importance.

see also...

- Adjustable hand levers GN 604.1 (Plastic, threaded stud Stainless Steel)
→ Main Catalogue Page 341
- Adjustable hand levers GN 604 (Plastic, threaded stud steel)
→ Main Catalogue Page 339

How to order

GN604.1-78-M10-25-SGA

1	l ₁
2	d ₁
3	l ₂
4	Finish