



elesa

Original design VDN.FP+IR-A

2 Bore code

B Without keyway

K With keyway DIN 6885-1 P9

4 Type

D With revolving retractable handle

1 d_1	3 d_2 H7 Bore	b	d_3	d_4	d_5	d_6	d_7	$l_1 -0,5$	$l_2 -0,5$	l_3	l_4	r	\varnothing Handle
100	10	26	24	22	35	54	39	12	33,5	51	56	37	22
125	12	28	32	26,5	44	70	46	15	38	57	56	48	22
150	14	30	32	26,5	50	80	48	15	38	60	65	57	23
175	16	32	40	33	55	90	56	15	43	66	80	68	26
200	20	32	40	33	55	90	60	15	43	68	90	76,5	28
225	20	33	49	40	66	110	66	15	44,5	71	90	88	28
250	22	36	49	40	66	110	70	15	44,5	75	90	101	28
300	26	36	58	58	94	148	82	18	56	87	90	124	28

Specification

Wheel body

Plastic, phenolic resin (PF)

- Reinforced
- Operating temperature -20 °C to +110 °C
- Black, shiny finish
- Flash mark polished

Hub bushing

Steel, blackened

Retractable handle

Plastic, phenolic resin (PF)

- Black, shiny finish
- Retracting mechanism
- Steel, blackened

RoHS

On request

- Without bore
- With safety-retractable handle (swivelling back automatically)

The handle in the handwheels GN 520.4 is locked in a conical bore in the operating position.

For reversal, it must first be pulled from the cone in axial direction.

A pressure spring holds the handle in both positions. When swung out, it automatically engages again.

see also...

GN 521.3 Handwheels with Retractable Handle (Polypropylene, bushing / retracting mechanism steel) QVX

GN 524.3 Handwheels with Retractable Handle (Polyamide, bushing / retracting mechanism steel) QVX

Technical Information

ISO Fundamental Tolerances QVX

Cross holes GN 110 QVX

Keyways P9 DIN 6885-1 QVX

Plastic Characteristics QVX

Accessory

GN 184 Countersunk Washers (for Axial Fixing) QVX

How to order

GN 520.4-200-K20-D

1 d_1

2 Bore code

3 d_2

4 Type

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

