



1 d <sub>1</sub>	3 d <sub>2</sub> H7 Bore		b	d <sub>3</sub>	d <sub>4</sub>	d <sub>5</sub>	d <sub>6</sub>	d <sub>7</sub>	h	l <sub>1</sub>	l <sub>2</sub>	l <sub>3</sub>	r	Ø Handle
	Type A	Type R												
100	10	10	24	22	20	30	25	27	9	22	34	60	39	15,5
125	-	12	28	26	24	35	28	31	11	27	39,5	60	49	18
150	14	14	32	26	24	38	30	34	10	30	44	65	58	22
200	20	20	39	40	38	50	40	44	13	36	53	90	81	25

Specification

<b>Wheel body</b>
Plastic, Polypropylene (PP)
• Reinforced, shock-resistant
• Operating temperature 0 °C to +80 °C
• Black, matte finish
<b>Hub bushing</b>
Stainless steel AISI 304
<b>Threaded bushing</b>
Brass
<b>Cover</b>
Plastic, light gray
<b>Revolving handle</b>
Plastic, Polyamide (PA)
• Black, matte finish
• Spindle
Stainless steel AISI 304

RoHS	<b>see also...</b>	<b>Page</b>
	GN 521 Disk Handwheels (Polypropylene, Hub Bushing Steel)	QVX
	GN 520.2 Disk Handwheels (Phenolic Resin, Hub Bushing Stainless Steel)	QVX

Disk handwheels GN 521.5 have recessed grips at their back. The cover conceals clamping elements, e.g. countersunk washers, as well as protruding and recessed shafts. For mounting, the cover is pushed in by hand. For dismantling, the cover can be raised and taken off by applying moderate pressure in the rim of the cover.

Technical Information	
Keyways P9 DIN 6885-1	QVX
Cross holes GN 110	QVX
ISO Fundamental Tolerances	QVX
Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX

<b>Accessory</b>	
<b>GN 184.5</b> Countersunk Washers (for Axial Fastening)	QVX

<b>How to order</b>  <b>GN 521.5-125-B12-R</b>	1 d <sub>1</sub>
	2 Bore code
	3 d <sub>2</sub>
	4 Type