



ELESA Original design ESP.



2 Type

- A Fixing with hexagon screw
- B Fixing with countersunk screw

1

$l_1$	$l_2 \pm 0,5$	$l_3$	$b_1$	$b_2$	$d$	$h_1$	$h_2$	$h_3$	$h_4$	$t$
114	93,5	74	35	19	6,5	33	7	11	9	5

Specification

- Plastic Technopolymer (Polyamide PA)
  - glass fiber reinforced
  - temperature resistant up to 110 °C
  - black gray, matte similar to RAL 7021
- Color of the cover (shiny):
  - black-gray, RAL 7021
  - orange, RAL 2004
  - gray, RAL 7035
  - yellow, RAL 1021
  - blue, RAL 5024
  - red, RAL 3000
- Strength properties → Page 1449
- Plastic characteristics → Page 1483
- RoHS

3

Information

The design of the ledge handles GN 630 matches the product family of Ergostyle®.

A typical application for ledge handles GN 630 is on double swing doors on machine shrouds or fixtures.

The ledge handles are protection for the operator's fingers. At the same time they shroud the two fixing screws of the ledge handle.

The cover is supplied loose.

see also...

- Product family Ergostyle® → Page 17
- Assembly sets for profile systems 30 / 40 GN 965 → Page 1428
- Assembly sets for profile systems 30 / 40 / 45 GN 968 → Page 1438

How to order

1 2 3  
GN630-114-B-DOR

1	$l_1$
2	Type
3	Color of the cover

