



**elisa**  
Original design CT.476 S-p



1 2 3

Steel									
d <sub>1</sub>	d <sub>2</sub>	Length l						b	h
20	M 4	6	10	-	-	-	-	9,5	11
25	M 5	10	16	-	-	-	-	11	13
32	M 5	10	16	20	-	-	-	13	15
32	M 6	10	16	20	25	30	40	13	15
32	M 8	16	20	25	40	45	-	13	15
40	M 5	10	16	20	-	-	-	15,5	17
40	M 6	16	20	25	30	40	-	15,5	17
40	M 8	16	25	40	-	-	-	15,5	17
40	M 10	20	30	40	-	-	-	15,5	17
48	M 8	16	25	-	-	-	-	19	19
56	M 10	20	30	-	-	-	-	21	23

1 2 3

Stainless steel									
d <sub>1</sub>	d <sub>2</sub>	Length l						b	h
20	M 4	6	10	-	-	-	-	9,5	11
25	M 5	10	16	25	-	-	-	11	13
32	M 6	10	16	20	25	30	40	13	15
32	M 8	16	20	25	30	40	-	13	15
40	M 8	16	25	40	-	-	-	15,5	17
48	M 8	16	25	-	-	-	-	19	19
56	M 10	20	30	-	-	-	-	21	23

**Specification**

4

- Plastic  
Technopolymer (Polyamide PA)  
- Glass fiber reinforced  
- Temperature resistant up to 130 °C  
- Black, matte finish
- Threaded stud  
- Steel —  
Zinc plated, blue passivated  
- Stainless steel AISI 303 **NI**
- *Plastic Characteristics* → Page 2158
- *Stainless Steel Characteristics* → Page 2166
- RoHS

**Information**

see also...

- *Wing Nuts GN 531.1 (with Protruding Hub)* → Page 617
- *Wing Screws GN 633* → Page 608
- *Stainless Steel Wing Screws GN 433* → Page 620
- *Stainless Steel Wing Screws GN 431* → Page 621

How to order (Threaded stud steel)

1	d <sub>1</sub>
2	d <sub>2</sub>
3	Length l

**GN 531-32-M6-20**

How to order (Threaded stud stainless steel)

1	d <sub>1</sub>
2	d <sub>2</sub>
3	Length l
4	Material

**GN 531-32-M6-30-NI**

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4