



4 Type

- A** Only with retaining ring
- H** With retaining cable
- K** With ball chain

d₁	d₂	Length l				d₃	h₁	h₂	h₃	r ≈	s
40	M 8	20	30	40	-	14	24	12	3,2	22,3	2,8
50	M 10	20	30	40	-	18	30	17	3,9	29,6	3,2
60	M 12	20	30	40	50	20	38	20	3,9	30,7	3,2

Specification

- Knob
Stainless steel AISI 316L
- Hub welded
- Matte, shot blasted
- Threaded stud
Stainless steel AISI 304
- Retaining ring GN 111.6
Stainless steel AISI 301
- Ball chain GN 111.5 (Type K)
Stainless steel AISI 301
- Retaining cable GN 111.2 (Type H)
Stainless steel
Coated with clear plastic
- *Stainless Steel Characteristics* → Page 2166
- RoHS

On request

- Ball chains / retaining cables with other lengths
- With spiral retaining cable GN 111.4
- Other GN / DIN standards with loss protection

Information

Stainless steel star knobs GN 5334.13 can be captive-attached to a base element with the help of a ball chain or a retaining cable.

The star knobs are supplied ready assembled (with retaining ring and ball chain or retaining cable).

Original ELESA design, now produced in metal in agreement with ELESA S.p.A.

see also...

- *Stainless Steel Ball Chains GN 111.5* → Page 1174
- *Stainless Steel Retaining Cables GN 111.2* → Page 1176
- *Spiral Retaining Cables GN 111.4* → Page 1175
- *Stainless Steel Retaining Rings GN 111.6* → Page 1179
- *Further Star Knobs with Loss Protection GN 111.7* → Page 2084

How to order

1	d₁
2	d₂
3	Length l
4	Type

GN 5334.13-60-M12-40-A

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4