



2 Type

- A Without dowel hole
- B With dowel hole



d₁ Thread	d₂ H7 Bore	d₃	d₄	d₅ H11	e	h	k	t
M 5	B 5	14	20	1,5	2,5	12	8	7
M 6	B 6	16	24	1,5	2,5	14	10	8
M 8	B 8	20	30	2	3	17	12	10
M 10	B 10	28	36	3	4	20	14	12
M 12	B 12	32	40	4	4	24	16	16

Specification

- Steel
 - Property class 5
 - Blackened
- *Strength Values of Nuts* → Page 2152
- *ISO Fundamental Tolerances* → Page 2151
- RoHS

Information

The dowel bore d_5 in the DIN 6303 knurled nut is designed for the use of clamping or notch pins.

Knurled nuts DIN 6303 with H7 bore and the size M12 are not provided for on the official standard sheet. In addition, the knurling divisions are larger than the DIN standard for better grip.

see also...

- *Quick Release Knurled Nuts GN 6303.1* → Page 644

How to order

DIN 6303-M8-A

1 **d₁** (d₂)

2 **Type**