



elisa
Original design VC.192-SST-p



Inox
Stainless
Steel

d₁	d₂	Length l					d₃	h₁ +1	h₂ +1
32	M 6	10	16	20	35	-	19	23	11
40	M 8	20	25	30	35	45	21	27	12
50	M 10	20	30	40	50	-	25	33	14
60	M 12	30	40	50	-	-	27	37	17

Specification

- Plastic
Duroplast (PF)
- Temperature resistant up to 110 °C
- Black, shiny finish
- Threaded stud
Stainless steel AISI 303
- *Plastic Characteristics* → Page 2158
- *Stainless Steel Characteristics* → Page 2166
- **RoHS**

Information

Star knobs GN 5337.5 with threaded stud meet highest quality requirements. Due to a special manufacturing process the mould parting line can be avoided.

Duroplast features very good chemical resistance.

The underside of the star knobs with threaded stud have no recess and therefore meet more stringent hygiene requirements.

see also...

- *Star Knobs with Threaded Stud GN 5337.4 (Technopolymer)* → Page 565
- *Star Knobs with Threaded Stud GN 5337.2 (Technopolymer)* → Page 561

How to order

GN 5337.5-40-M8-25

1	d ₁
2	d ₂
3	Length l

