


Assembly instruction



2 Type
S With snap ring



d ₁	d ₂ H12	d ₃	e ≈	h ₁	h ₂	Suitable for grub screw DIN 6332	
12	4,6	10	2,1	7	2,5	M 6	-
16	6,1	12	3	9	4	M 8	-
20	8,1	15	3,6	11	5	M 10	M 12
25	8,1	18	4,6	13	6	M 10	M 12
32	12,1	22	5,4	15	7	M 16	-
40	15,6	28	5,5	16	9	M 20	-

Specification

- Steel
- Case-hardened
- Blackened
- Snap ring
- Spring steel wire
- ISO Fundamental Tolerances → Page 2151
- RoHS

Accessory

- Grub Screws DIN 6332 → Page 1065
- Tommy Screws DIN 6304 → Page 512
- Tommy Screws DIN 6306 → Page 513

Information

Thrust pads DIN 6311 are used with grub screws DIN 6332 and tommy screws DIN 6304 or DIN 6306. Due to the pivoting connection between the thrust pin and thrust pad, they adapt to clamping surfaces that are uneven or not perpendicular to the screw axis, and at the same time prevent transmission of the rotational movement of the screw to the clamping surface during clamping.

Assembly is made easier if the thrust pin is positioned at an angle against the closed side of the snap ring and then pressed it in, see assembly instruction.

see also...

- Thrust Pads GN 6311.1 → Page 1069
- Foot Plates GN 6311.3 (Steel) → Page 1067
- Foot Plates GN 6311.5 (Steel Stainless) → Page 1068

How to order

DIN 6311-40-S

1 d₁

2 Type