



elesa
Original design VC.192+F / VC.192+IN

- Type**
- S** With face and pointer
 - Z** With pointer

d₁		d₂ H9 Bore	d₃	d₄	d₅	d₆	d₇	e	h₁	h₂	h₃	h₄	h₅	l₁	l₂
Type S	Type Z														
32	-	B 6	14	19	-	M 4	36	6	27	-	3	-	19	19	-
40	40	B 6	14	21	25	M 4	45	6	30	27	3	2	14	24	25
50	50	B 8	15	25	30	M 5	56	7	36	33	3	2	20	30	31
60	60	B 8	15	27	32	M 5	70	7	42	37	5	2	20	37	38
70	70	B 10	18	30	35	M 6	80	10	48	44	5	2	25	42	45

Specification

Handle
Plastic, phenolic resin (PF)
• Operating temperature -20 °C to +110 °C
• Black, shiny finish

Pointer
Plastic, Polyamide (PA)
• Operating temperature -20 °C to +110 °C
• Black, shiny finish
• Arrow for type S in white design

Bushing
• d₁ = 32, 40: Brass
• d₁ = 50, 60, 70: Steel, blackened

Grub screw DIN 916
Stainless steel
with internal hex and serrated point

RoHS

Setting knobs GN 5338 are very appealing with a good gripping feel. The manufacturing technique has made it possible to produce them with no visible flash mark.

Two studs with a serrated point ensure proper fastening on the shaft.

Technical Information	Page
ISO Fundamental Tolerances	QVX
Plastic Characteristics	QVX

How to order GN 5338-50-B8-S	1	d ₁
	2	d ₂
	3	Type