


**Application example**



**Type**

- N** Without plastic cap
- G** With plastic cap, gliding
- R** With plastic cap, non-gliding



<b>d<sub>1</sub></b>		<b>h</b>	<b>d<sub>2</sub> +0,2</b>	<b>e ≈</b>	<b>s</b>	suitable for grub screw DIN 6332
Type N / R	Type G					
50	50	11,5	9,2	3,7	2	M 12
50	50	13,5	12,5	4	2	M 16
60	60	13,5	12,5	4	2	M 16
60	60	15,5	16,5	4,3	2	M 20
80	-	18	12,5	8	2,5	M 16
80	-	20	16,5	8,3	2,5	M 20
100	-	20	12,5	11	3	M 16
100	-	22	16,5	11,3	3	M 20

**Specification**

- Foot plate  
Steel zinc plated, blue passivated
- Retaining spring  
Stainless steel AISI 301
- Plastic caps
  - Type G  
Technopolymer (Polyacetal POM)  
Cream RAL 9001
  - Type R  
Elastomer (TPE)  
Hardness ≈ 75 Shore A  
Black
- *Plastic Characteristics* → Page 2158
- *Stainless Steel Characteristics* → Page 2166
- **RoHS**

**Accessory**

- Grub Screws DIN 6332 → Page 1065
- Tommy Screws DIN 6304 → Page 512
- Tommy Screws DIN 6306 → Page 513

**Information**

Foot plates GN 6311.3 are used in connection with screws with pivots (grub screws DIN 6332, tommy screws DIN 6304, DIN 6306) for installing and leveling devices and mechanisms.

Owing to the special shape of the retaining spring, the foot plate is easily plugged onto and removed from the pivot.

The types G and R with plastic cap prevent damage to sensitive surfaces. Due to the large plate diameter  $d_1$ , the contact pressure remains within tolerable limits.

**see also...**

- *Leveling Feet GN 6311.4 (Steel)* → Page 1434
- *Leveling Feet GN 6311.6 (Stainless Steel)* → Page 1435
- *Thrust Pads DIN 6311* → Page 1066
- *Thrust Pads GN 6311.1* → Page 1069

**How to order**

**GN 6311.3-60-15,5-N**

- 1**  $d_1$
- 2** h
- 3** Type

