



3 Type

- N** Without plastic cap
- G** With plastic cap, gliding
- R** With plastic cap, non-gliding

Application example



1

2

d₁		h	d₂ +0,2	e ≈	s	suitable for grub screw DIN 6332
Type N / R	Type G					
50	50	11,5	9,2	3,7	2	M 12
50	50	13,5	12,5	4	2	M 16
60	60	13,5	12,5	4	2	M 16
60	60	15,5	16,5	4,3	2	M 20
80	-	18	12,5	8	2,5	M 16
80	-	20	16,5	8,3	2,5	M 20
100	-	20	12,5	11	3	M 16
100	-	22	16,5	11,3	3	M 20

Specification

- Foot plate
Stainless steel AISI 304
- Retaining spring
Stainless steel AISI 301
- Plastic caps
 - Type G
Technopolymer (Polyacetal POM)
Cream RAL 9001
 - Type R
Elastomer (TPE)
Hardness ≈ 75 Shore A
Black
- *Plastic Characteristics* → Page 2158
- *Stainless Steel Characteristics* → Page 2166
- RoHS

Information

Foot plates GN 6311.5 are used in connection with screws with pivots (Grub screws DIN 6332) for installing and leveling devices and mechanisms.

Owing to the special shape of the immovable retaining spring, the foot plate is easily plugged onto and removed from, the pivot.

The types G and R with plastic cap prevent damage to sensitive surfaces. Due to the large plate diameter d_1 , the contact pressure remains within tolerable limits.

see also...

- *Leveling Feet GN 6311.4 (Steel)* → Page 1434
- *Leveling Feet GN 6311.6 (Stainless Steel)* → Page 1435
- *Thrust Pads GN 6311.1 (Steel / Stainless Steel)* → Page 1069
- *Thrust Pads DIN 6311 (Steel)* → Page 1066

Accessory

- Grub Screws DIN 6332 → Page 1065

How to order

GN6311.5-50-11,5-R

- 1** d_1
- 2** h
- 3** Type