



3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9

¹ h	² d ₁	d ₂	e min.	Length l	s
10	M 6	8	11,5	11	10
15	M 8	10	15	13	13
20	M 6	6	11,5	11	10
20	M 10	13	19,6	16	17
25	M 12	15	21,9	20	19
30	M 8	9	15	13	13
40	M 10	13	19,6	16	17
50	M 12	15	21,9	20	19

Specification

- Steel (German Material No. 1.0718)
 - Not hardened
 - Blackened
- RoHS

Information

Feet DIN 6320 are normally used in jig construction if neither a self-aligning support nor an axial adjustment is required. Unlike the models specified in the official standard sheet, these feet are made of 1.0718 steel.

How to order	¹ h
	² d ₁
DIN 6320-20-M6	