



1

d <sub>1</sub>	d <sub>2</sub>	a	e min.	m	A/F
M 6	14	3	11,5	9	10
M 8	18	3,5	14,4	12	13
M 10	22	4	17,8	15	16
M 12	25	4	20	18	18
M 14	28	4	24,6	21	22
M 16	31	5	26,8	24	24
M 20	37	6	33,5	30	30
M 24	45	6	40	36	36
M 30	58	8	51,3	45	46
M 36	68	10	61,3	54	55

**Specification**

- Steel
  - Property class 10
  - Blackened
- *Strength Values of Nuts* → Page 2152
- RoHS

**On request**

- Size M10 with A/F = 17

**Information**

Hex nuts DIN 6331 are used on clamping applications which require frequent clamping and unclamping ( $m = 1,5 \times d_1$ ).

The collar of the nut eliminates the need for washers.

The official standard sheet specifies the additional sizes M 27, M 42 and M 48. But M 14 is not foreseen on the official standard sheet.

How to order

**DIN 6331-M16**

1 d<sub>1</sub>

