



<b>b</b>	Length <b>l</b> ±0,25	<b>a</b>	<b>d<sub>1</sub></b>	<b>d<sub>2</sub></b>	<b>h</b>	<b>r</b>	<b>t</b> min.
25	112	16	M 6	10	50	5	10
25	128	16	M 6	10	54	7	10
25	160	16	M 6	10	54	9	10
25	192	16	M 6	10	54	9	10
35	160	25	M 8	17	68	12,5	12
35	192	25	M 8	17	68	12,5	12
35	300	25	M 8	17	68	12,5	12

**Specification**

**Sheathing**

- Thermoplastic polyurethane (TPU)
- Black, textured matte finish
- Elastic, 65±5 Shore A
- Operating temperature up to 70 °C
- Abrasion-resistant
- Insulating
- Weather-proof

**Handle core**

- Stainless steel AISI 303  
Round (for size b = 25)
- Aluminum  
Elliptical (for size b = 35)

RoHS

**On request**

- Other colors

The shock absorbing casing of the GN 564 cabinet U-handles made of thermoplastic polyurethane (TPU) offers protection from injuries, while its elliptical shape gives it a nice hold.

The stainless steel core and the aluminum core guarantee a high basic durability of the handle.

**see also...**

	<b>Page</b>
<b>GN 565</b> Cabinet U-Handles (Aluminium)	QVX
<b>GN 725</b> Cabinet U-Handles (Polypropylene)	QVX

**Technical Information**

Product Family Softline	QVX
Load Rating Information	QVX
Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX

**How to order**

**GN 564-25-128**

<b>1</b>	<b>b</b>
<b>2</b>	<b>Length l</b>

