



3 Type

- E** with threaded blind bore
- C** with plain blind bore, Tol. H7

d ₁	d ₂				d ₃ H7 GN 6335.1 GN 6335.2 Type C Bushing steel	d ₄	h ₁	h ₂ ≈	h ₃	t min.
	GN 6335.1 Type E Bushing steel	GN 6335.2 Type E Bushing steel	Bushing SST							
32	M 6	M 6	-	M 6	B 6 -	12	20	10	9	12
40	M 8	M 6	M 8	M 8	B 6 B 8	14	25	13	10	14
50	M 10	M 8	M 10	M 10	B 8 B 10	18	32	20	12	18
63	M 12	M 10	M 12	M 12	B 10 B 12	20	40	25	14	22
80	M 16	M 12	M 16	M 16	B 16 -	25	50	30	17	30

Specification

- **GN 6335.1**
Plastic
Duroplast (PF)
Black, shiny finish
Bushing
Steel zinc plated, blue passivated —
- **GN 6335.2**
Plastic
Technopolymer (Polyamide PA)
- Shock-resistant
- Black, matte finish
Bushing
- Steel
Zinc plated, blue passivated —
- Stainless steel AISI 303 **NI**
- *ISO Fundamental Tolerances* → Page 2151
- *Plastic Characteristics* → Page 2158
- **RoHS**

Information

Hand knobs GN 6335.1 / GN 6335.2 with protruding steel bushing have important advantages:

The face of the bushing is exactly square to the bore and is with the complete diameter out of steel or stainless steel. The protruding steel bushing allows a perfect cross-dowels connection.

How to order (Duroplast, bushing steel)	1	d ₁
	2	d ₃ (d ₂)
	3	Type
GN 6335.1-50-B10-C		

How to order (Technopolymer, bushing SST)	1	d ₁
	2	d ₂ (d ₃)
	3	Type
	4	Material (Bushing)
GN 6335.2-63-M12-E-NI		