




3 Type

- A** Mounting from the back (threaded blind bore)
B Mounting from the operator's side

b	Length l			a	d ₁	d ₂	h ₁	h ₂	r	t ₁ min.	t ₂
	Type A shot-blasted GS	Type A slip polished GP	Type B shot-blasted GS								
20	112	112	112	13	M 6	5,4	49	13,5	13	10	5,5
20	128	128	128	13	M 6	5,4	51	13,5	13	10	5,5
20	160	160	160	13	M 6	5,4	51	13,5	13	10	5,5
20	200	200	-	13	M 6	-	51	-	13	10	-
20	250	-	-	13	M 6	-	51	-	13	10	-
20	300	-	-	13	M 6	-	51	-	13	10	-
20	400	-	-	13	M 6	-	51	-	13	10	-
26	128	128	128	17	M 8	6,4	57	11	19	12	6
26	160	160	160	17	M 8	6,4	57	11	19	12	6
26	200	200	200	17	M 8	6,4	57	11	19	12	6
26	300	-	-	17	M 8	-	57	-	19	12	-
26	400	-	-	17	M 8	-	57	-	19	12	-
26	500	-	-	17	M 8	-	57	-	19	12	-

Specification

Stainless steel AISI 304

- Matte shot-blasted finish
- Slip polished, shiny metallic (only type A)

4

**GS
GP**

RoHS

The special features of cabinet U-handles GN 565.5 are their rigidity and ergonomic shaping.

Cabinet U-handles are manufactured from a bent profile.

see also...	Page
GN 565 Cabinet U-Handles (Aluminium)	QVX
GN 565.1 Cabinet U-Handles (Aluminum)	QVX
GN 425 Cabinet U-Handles (Stainless Steel)	QVX
GN 426.5 Cabinet U-Handles (Stainless Steel)	QVX
GN 728.5 Cabinet U-Handles (Stainless Steel, Mounting from the Back or the Operator's Side)	QVX

Technical Information

Load Rating Information	QVX
Stainless Steel Characteristics	QVX

Accessory

GN 181 Fastening Sets (Mounting from the Operator's Side)	QVX
--	-----

How to order	1 b
	2 Length l
	3 Type
GN 565.5-20-128-B-GS	4 Finish