



Length l	d ₁ H7 Bore GN 570	S H9 Square GN 570.1	d ₂	d ₃	d ₄	d ₅	h ₁	h ₂	h ₃	h ₄	h ₅	h ₆	h ₇	h ₈ ≈	Ø Handle	
50	B 6	-	V 6	16	13	23	-	28	31	18	21	10	10	11	28,5	14
64	B 8	B 10	V 8	18	16	27	18	29	33	19	23	10	10	13	42,5	18
80	B 10	-	V 10	22	17	30	20	32	36	22	26	10	13	13	52,5	21
100	B 12	-	V 12	24	21	34	25	37	40	27	30	10	15	16	67,5	23
130	B 14	-	V 14	28	25	40	28	44	49	30	35	14	20	16	82,5	26
160	B 16	-	V 17	34	27	45	30	49	55	34	40	15	23	18	92,5	28
210	S 12*	-	-	40	31	50	-	53	60	-	-	15	26	20	92,5	28

* Blind hole (pilot bore)

Specification

Body

- Plastic, Polyamide (PA)
- Glass fiber reinforced
- Operating temperature 0 °C to +90 °C
- Black, matte finish

GN 570

Cover

Aluminum
anodized, natural color

Hub bushing

Steel, blackened

Threaded bushing to accept the revolving handle

Brass

Revolving handle GN 598

- Plastic, polypropylene (PP)
- Black, matte finish
- Black, glossy for size 14
- Spindle steel
- Zinc plated, blue passivated

RoHS

The protruding steel bushing of cranked handles GN 570 / GN 570.1 ensures an accurate bore and square to bore face. It can be retained with a pin or a retaining screw. The link between the cranked handle and shaft can be established either with a keyway or a follower pin.

see also...

	Page
GN 570.2 Cranked Handles (Plastic)	QVX
GN 471 Cranked Handles (Aluminum)	QVX
GN 471.1 Cranked Handles (Zinc die casting)	QVX
GN 670 Cranked Handles (Plastic)	QVX

Technical Information

Cross holes GN 110	QVX
Squares DIN 79	QVX
ISO Fundamental Tolerances	QVX
Plastic Characteristics	QVX

How to order (with bore)

GN 570-64-B8	1 Length l
	2 d ₁

How to order (with square)

GN 570.1-100-V12	1 Length l
	2 s