



3 Type

- L Angled lever with plain bore
- N Angled lever with threaded bore

1 l_1	2 d_1 Thread	2 d_2 H7 Bore	b	d_3	d_4	d_5	d_6	$h \approx$	$l_2 \approx$
63	M 8	B 8	12	16	12,5	20	8	33	60
80	M 10	B 10	14,5	20	16	20	9	40	76
100	M 12	B 12	18,5	25	20	25	11	50	95
125	M 16	B 16	24	32	25	32	15	63	119
160	M 20	B 20	30	40	31	40	18	80	152

Specification

Hub / Shaft

- Steel
- Turned
- Blackened

Ball knobs DIN 319

- Plastic, phenolic resin (PF)
- Black

RoHS

The official DIN standard sheet specifies additional sizes 200 - M24 / B24.

see also...

	Page
GN 6337.3 Adjustable Clamping Levers	QVX
DIN 99 Clamping Levers	QVX
GN 212 Tension Levers	QVX

Technical Information

ISO Fundamental Tolerances	QVX
Plastic Characteristics	QVX

How to order

DIN 6337-100-M12-N

1	l_1
2	d_1 (d_2)
3	Type

