



**elesa**  
Original design MT-AT+IR

Length l	d <sub>1</sub> H9	d <sub>2</sub>	d <sub>3</sub>	d <sub>4</sub>	h <sub>1</sub>	h <sub>2</sub>	h <sub>3</sub>	h <sub>4</sub>	h <sub>5</sub> ≈	t min.	Ø Handle
64	B 8	15	20	26,5	31,5	17,5	13,5	14	45	18	16
80	B 10	18	24	30	37	23,5	13,5	14	60	23	18
100	B 12	18	24	33,5	40,5	25	14	18,5	65	22	22
130	B 14	26	34	39	49	34	15	18,5	65	28	22
160	B 16	26	34,5	44	54,5	36	18	18,5	80	28	24

## Specification

### Body

- Plastic, Polyamide (PA)
- Glass fiber reinforced
- Operating temperature 0 °C to +90 °C
- Black, matte finish

### Hub bushing

Steel, blackened

### Retractable handle

- Plastic, Polyamide (PA)
- Black, matte finish
- Retractable mechanism
- Steel, blackened

RoHS

Cranked handles GN 570.3 are connected to a shaft by means of a cross pin and are used for applications where the handpiece has to stay occasionally in its retracted position.

The handle is pulled out of its taper seating in the direction of the arrow and then tilted.

A pressure spring locks the handle in both end positions.

A positive lock is achieved in the operating position by way of a taper seating.

see also...

	Page
<b>GN 471.3</b> Cranked Handles with Retractable Handle (Aluminum)	QVX
<b>GN 472.3</b> Cranked Handles with Retractable Handle (Aluminum)	QVX

### Technical Information

Cross holes GN 110	QVX
ISO Fundamental Tolerances	QVX
Plastic Characteristics	QVX

### How to order

**GN 570.3-64-B8**

1	Length l
2	d <sub>1</sub>