



4 Type

- A** with cylindrical bore
- B** with bore for countersunk screw

2

3

d_1 ^{+0,5 +0,2}	d_2		d_3 Type B	s
4	10	13	8,4	2,5
5	13	16	10,5	3
6	15	20	12,6	4
8	20	26	16,8	5
10	25	32	21	6,5
12	30	40	25,2	7,5

Specification

1

5

- Steel **ST**
- turned **BT**
- blackened **ZB**
- zinc plated, blue passivated
- Stainless Steel AISI 303 **NI**
- turned
- matt shot-blasted **MT**
- *Stainless Steel characteristics* → Page 1489
- **RoHS**

Information

Washers GN 6341 are used mainly in mechanical machine and jig construction when DIN 125, DIN 9021 and DIN 6340 washers no longer meet requirements.

In particular, Type B for countersunk screws is ideal for solid screw connections with a low construction height.

see also...

- *Heavy duty washers GN 6339* → Page 812
- *Countersunk washers GN 184* → Page 814
- *Washers DIN 6340* → Page 816

How to order

1	Material
2	d_1
3	d_2
4	Type
5	Finish

GN6341-ST-8-26-B-ZB