



elesa
Original design BT-SST / SST-FP



- 3 Type**
- D** With threaded through bore
 - E** With threaded blind bore

1 d ₁	2 d ₂ Type D	2 d ₃ Type E		d ₄	h	k	t ₁ min.	t ₂	
16	-	M 3	M 4	M 5	11	13	8	6	-
20	M 5	M 5	M 6	-	11,5	16	10	5	12
25	M 6	M 6	-	-	16	19	11	8	14
32	M 8	M 8	-	-	17	22	13	10	16

Specification

Knob

- Plastic, Polyamide (PA)
- Reinforced
- Operating temperature -30 °C to +130 °C
- Black, matte finish

Bushing

Stainless steel AISI 303

RoHS

Knurled nuts GN 590.5 are used for quick, tool-free mounting or adjusting of fixtures and devices.

With the stainless steel threaded bushings, they are also suitable for applications that place increased demands on the corrosion resistance of the components used.

see also...	Page
GN 590 Knurled Nuts (Bushing Steel)	QVX
GN 420 Knurled Nuts	QVX

Technical Information

Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX

How to order

GN 590.5-32-M8-E

- 1** d₁
- 2** d₂ (d₃)
- 3** Type

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

