


Type A



Type E



ELESA original design I.281/I.281+x-SST



- 4 Type**
- A** with threaded bolt
 - E** without threaded bolt

2 d_1	3 d_2 6g Type A		3 d_3 ^{+0.3} / _{+0.1} Type E	d_4	d_5	l_1	l_2	l_3	l_4	l_5	A/F
18	M 6	-	8	15	12	40	13	0,3	39	35	4
21	M 8	-	10	17	14	50	15	0,5	49	43	5
23	M 8	M 10	12	19	16	65	17	0,5	64	56	6
26	M 10	-	13	21	17	80	18	0,5	79	70	6
28	M 10	-	14	22	19	90	18	0,5	89	79	8
31	M 12	-	16	25	20	102	20	1	100	89	8

Specification

- Plastic
Duroplast (Phenolic PF)
- temperature resistant up to 110 °C
- black, shiny finish
- Threaded bolt
Stainless Steel AISI 304
- *Plastic characteristics* → Page 1483
- *Stainless Steel characteristics* → Page 1489
- **RoHS compliant**

1 Information

KU The outstanding feature of revolving handles GN 598.2 is their highly robust design. Type E is suitable for use in connection with user-specific threaded bolts.

see also...

- *Revolving handles GN 598.1 (Spindle Stainless Steel)* → Page 36

How to order (with threaded bolt)

1 **2** **3** **4**
GN 598.2-KU-31-M12-A

1	Material
2	d_1
3	d_2
4	Type

How to order (without threaded bolt)

1 **2** **3** **4**
GN 598.2-KU-26-13-E

1	Material
2	d_1
3	d_3
4	Type

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4